

# MicroVantage™ MAS-E Series

Electronic Grade Polyethersulfone Membrane Filter Cartridges

# MicroVantage Ultra Premium Filter Series



- Absolute retention ratings from 0.03 to 0.65 microns
- 7.2 square feet (0.67 m<sup>2</sup>) of media surface area per ten inch length for optimal performance
- Fully integrity tested to ensure reliable performance in critical applications
- 100% flushed with 18 megohm DI water to less than 5 ppb TOC
- Rapid rinse-up to 18 megohm resistivity and low extractables for use in ultrapure water
- Manufactured in a Class 10,000 Clean Room environment for high purity
- Rigid, molded cage protects pleated media and strengthens structural stability
- Complies with Food & Drug Administration's CFR criteria for food & beverage contact
- Meets USP Class VI Biological Test for plastics
- Available in standard lengths and end cap configurations to fit most filter housings
- Produced up to 40 inches in length (10 inch modules)

## Applications

Semiconductor

Microelectronics

Process Water

DI Water

RO Pre/Post Filtration

Water & Wastewater

## Specifications & Operating Parameters

**Pore Sizes** 0.03, 0.1, 0.2, 0.45, 0.65 microns absolute retention

**Nominal Lengths** 9.75" (24.7 cm), 10" (25.4 cm), 20" (50.8 cm), 30" (76.2 cm), 40" (101.6 cm)

**Outside Diameter** 2.67" (6.78 cm)

**Inside Diameter** 1.0" (2.54 cm)

**Media Surface Area** 7.2 sq.ft. (0.67 m<sup>2</sup>) per 10 inches filter length

### Gaskets/O-rings

Silicone, Buna N, EPR, Viton, Teflon Encapsulated Viton (O-rings only)

### Materials of Construction

Filter Media: Polyethersulfone  
Outer Cage: Polypropylene  
Inner Core: Polypropylene  
End caps: Polypropylene

**Maximum Operating Temperature** 176°F (80°C)

**Recommended Change-out Differential Pressure** 35 psid (2.4 bar)

### Maximum Differential (Collapse) Pressure

75 psid @ 70°F (5.2 bar @21°C), 40 psid @176°F (2.8 bar @ 80°C)

### Sanitization and Sterilization

Hot water at 175°F (80°C) at 5 psid for 30 minutes

In-line steam at 257°F (125°C) @ 1 psid (0.07 bar) for 30 minutes


Autoclavable at 257°F (125°C) for 30 minutes

### FDA and USP Compliance

All filters are manufactured of virgin polypropylene materials with no additives or other manufacturing agents. All polypropylene materials comply with the requirements of Food and Drug Administration Title 21 of The Code of Federal Regulations 174.5, 177.1520 and 177.1630. All components meet current USP Class VI biological tests for plastics

## Flow vs. Pressure Drop

## Integrity Testing



PORE SIZE	AIR DIFFUSION RATE
0.03 µm	≤30cc/min@60psi
0.1 µm	≤30cc/min@48psi
0.2 µm	≤30cc/min@35psi
0.45 µm	≤30cc/min@20psi
0.65 µm	≤30cc/min@15psi
<b>Per 10" length water wetted membrane</b>	

This chart represents the typical water flow per 10" cartridge length. Cartridges are tested in water at ambient temperature. Data may be extrapolated for multiple lengths, but as flow rate increases, ΔP of the housing becomes more apparent.

## Ordering Guide (Example: MAS0.2-10S4S-E)

MAS	0.2	10	S4	S	-	E	
PRODUCT CODE	MICRON	LENGTH	END CAP CONFIGURATION	GASKET/O-RING		GRADE	OPTION
MAS	0.03 0.1 0.2 0.45 0.65	9.75" 10" 19.75" 20" 29.25" 30" 40"	S1 = DOE S3 = 222 w/ Fin End S4 = 222 w/ Flat End S5 = 226 w/ Fin End S6 = 226 w/ Flat End S7 = Internal O-ring with Recessed Plug S9 = Internal O-ring on both ends	B = Buna N E = EPDM S = Silicone V = Viton T = Teflon encapsulated Viton (O-ring only)		E = Electronic	HT = High Temperature*

\* High Temperature construction (cage, core, end caps): Maximum Temperature 200°F (93.3°C) - Available only in 222 or 226 with Fin or Flat end caps.

## Filter Housings

Shelco manufactures a full line of filter housings. From our rugged single cartridge housings to our heavy duty multi-cartridge housings. Shelco is the perfect choice for your filtration solutions.